





Technisches Datenblatt

Produkt / Typ	LiBa®Box M <i>Transport- und Lager Box für Lithiumbatterien</i>
Außenmaße L x B x H in mm (ca.)	1200 × 800 × 990 mm
Innenmaße L x B x H in mm (ca.)	1050 × 660 × 500 mm
Nettogewicht in kg (ca.)	ca. 176 kg
Max. Bruttomasse in kg (ca.)	590 kg
Bauart	Stahlkonstruktion
Hersteller	GelKoh GmbH
Produktionsjahr	Ab 2018
UN-Codierung	4A/X
Anwendbar mit	SV310, SV376, SV377, LP905, LP904, LP906 und LP903 gem. ADR / Verpackungsanweisung
Löschanlage	LiBa®Sol
Auslösung	Selbstzündend ab ca. 180°C
Auffangwanne	Auffangwanne für gewässergefährdende Stoffe nach StawaR
Innenverpackung	LiBa®Bag, LiBa®Safe, LiBa®Barrel
Sonstiges	Kranbar, Staplergeeignet, Erdungsanschluss, Seriennummer, Lüftungsflächen
Zubehör	Regal, Steckrollen, Regenhaube, Zurrgurte, Magnettafeln, Innenverpackung gemäß ADR

Der Hersteller bescheinigt hiermit die Eigenüberwachung des Erzeugnisses, sowie das durch die BAM anerkannte QS-System. Die Herstellung erfolgte zeichnungs- und normgerecht. (Je nach Ausführung Abbildung ähnlich / Änderungen vorbehalten!)



Spec Sheet

Product / Variant	LiBa®Box M <i>Transport and storage container for lithium batteries</i>
Outer dimensions L x W x H in mm (approx.)	1200 × 839 × 990 mm
Inner dimensions L x W x H in mm (approx.)	1050 × 660 × 500 mm
Net weight in kg (approx.)	ca. 176 kg
Max weight (approx.)	590 kg
Construction	Steel construction
Manufacturer	GelKoh GmbH
Production year	Since 2018
UN code	4A/X
Usable with	SV310, SV376, SV377, LP905, LP904, LP906 und LP903 in accordance with ADR / Packaging instructions
Extinguishing system	LiBa®Sol
Trigger	Automatic trigger at approx. 180°C
Spill containment	Spill containment for substances hazardous to waters, according to StawaR
Inner packaging	LiBa®Bag, LiBa®Safe, LiBa®Barrel
Others	Craneable, forklift suitable, ground connection, serial number, ventilation surfaces
Accessories	Rain cover, shelf, plug-in wheels, lashing straps, magnet labels, inner packaging in accordance with ADR

The manufacturer hereby certifies the self-monitoring of the product as well as the QS system recognised by BAM.
The manufacture was carried out in accordance with the drawings and standards.
(Depending on version, illustration similar / subject to change!)